



FD67CG57, Substation - Copper Stud Connector

By Burndy
Catalog # [FD67CG57](#)

Copper Stud Connectors



Features

- High copper alloy stud connector allows bolting cable and tubing terminals to equipment studs
- Hex head captured bolts provide one-wrench installation
- One pad contact surface is on centerline of stud, pad is finished on both sides, all pads are 4-hole NEMA drilling

Application

Substation

Specifications

Standards - RoHS Compliance	UI
Status	
Certification - CSA Approved	No

Conductor

Conductor - Connection Combination	Stud to Pad
------------------------------------	-------------

Configuration

Physical Attribute - Pad Orientation	In-line
--------------------------------------	---------

Connector Type	Stud Connector
----------------	----------------

Dimensions

Dimension - Pin Diameter inch	1.500 in
Dimension - Height mm	0 mm
Dimension - Threads per inch	12

General

Plated	N
Material - Hardware	DURIUM™ Silicon Bronze
UPC	621945144439
Type	Studs
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	621945144439
UPC 14 Digit GTIN	00621945144439

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)