



GCM29CG3, Mechanical Grounding Connector, 2 Cables to Bar

By Burndy
Catalog # [GCM29CG3](#)

Mechanical Grounding Connector, 2/0 AWG (Sol) - 250 KCMIL, 1/4" Stud, Bright Dip



Features

- High copper alloy ground connector for joining a wide range of 2 parallel cables to 1/2" thick bar
- Type GC separates cable from bar
- Type GCM clamps cable direct to bar surface
- One wrench installation
- UL467 Listed
- Suitable for Direct Burial in earth or concrete

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	UL467
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size	• 2/0 AWG • 3/0 AWG • 4/0 AWG
Conductor - Copper Solid Size Range	2/0 AWG - 250 KCMIL
Conductor - Copper Str Size Range	2/0 AWG - 250 kcmil
Conductor - Copper Str Size	• 2/0 AWG • 3/0 AWG • 4/0 AWG

- 250 kcmil

Dimensions

Package Height	0.000 in
Dimension - Height mm	58.7 mm
Dimension - Height inch	2.31 in
Package Weight	0.000 lb.
Dimension - Width mm	51 mm
Dimension - Width inch	2.00 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	41 mm
Dimension - Width fraction	2 in
Dimension - Length Overall inch	1.62 in

Force Related

Installation Torque	480 lb-in
Recommended in-lb	

General

Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
UPC	781810424322
Material Type - Screw	DURIUM™ Silicon Bronze
Material	Copper Alloy
Plating Type	Bright Dip
UPC 12 Digit	781810424322
UPC 14 Digit GTIN	00781810424322

Product Assets

[Catalog \[English\]](#)