



GCM34W, Mech Ground, 2 Cables to Bar, Tin Plated

By Burndy

Catalog # [GCM34W](#)

Mechanical Ground Connector, 2 Copper Cables to 1/4" Thick Bar, 300-500 kcmil Cu



Features

- High copper alloy ground connector for joining a wide range of 2 parallel cables to 1/2" thick bar
- Type GC separates cable from bar
- Type GCM clamps cable direct to bar surface
- One wrench installation
- UL467 Listed
- Suitable for Direct Burial in earth or concrete

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size Range	300 kcmil - 500 kcmil
Conductor - Copper Str Size	• 300 kcmil • 350 kcmil • 400 kcmil • 450 kcmil • 500 kcmil

Dimensions

Dimension - Bar Width inch	2.44 in
Dimension - Bar Thickness mm	6 mm
Dimension - Bar Width mm	62 mm

Dimension - Bar Thickness inch	0.25 in
Package Height	0.000 in
Dimension - Height mm	65.3 mm
Dimension - Height inch	2.57 in
Package Weight	0.000 lb.
Dimension - Width mm	62 mm
Dimension - Width inch	2.44 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - Bar Length mm	41 mm
Dimension - L Length Overall mm	41 mm
Dimension - Bar Length inch	1.62 in
Dimension - Width fraction	2-4/9 in
Dimension - Length Overall inch	1.62 in

Force Related

Installation Torque	480 LBS/in
Recommended in-lb	

General

Physical Attribute - Screw Type	Hexagonal Bolt
Plated	Y
UPC	781810213254
Material Type - Screw	DURIUM™ Silicon Bronze
Material	Copper Alloy, Cast
Plating Type	Tin Plated
UPC 12 Digit	781810213254
UPC 14 Digit GTIN	00781810213254

Logistics

Minimum Pack Quantity	25
Pallet Quantity	3024
Carton Quantity	12

Product Assets

[Catalog \[English\]](#)