



GD2229, Mech Ground Conn, 2 Cables to Rod or Pipe

By Burndy
Catalog # [GD2229](#)

Mechanical Grounding Connector, 2 Parallel Cables to Rod or Pipe, 2/0 AWG (Sol.) - 250 kcmil, 4" to 4-1/2" Rod, 4" Pipe

Features

- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets
- One-wrench installation

Application

For Joining A Range Of Two Parallel Copper Cables To Rod Or Pipe And Burial In Ground Or Concrete

Specifications

Certification - UL Recognized	No
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - UL Listed Direct Burial	Yes
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	• 2/0 • 3/0 • 4/0 • 250
Conductor Size	2/0 AWG Sol - 250 kcmil
Conductor - Copper Solid Size	• 2/0 • 3/0 • 4/0
Conductor - Copper Solid Size Range	2/0-4/0
Conductor - Copper Str Size Range	2/0 AWG - 250 kcmil
Conductor - Copper Str Size B Range	4



Conductor - Copper Tube Std Size Range	4
Conductor - Copper Tube Std Size	4

Dimensions

Package Height	0.000 in
Dimension - Height mm	162.1 mm
Dimension - Height inch	6.38 in
Dimension - Height fraction	6-3/8 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Width fraction	5-7/8 in
Dimension - Width mm	148 mm
Dimension - Width inch	5.81 in
Dimension - B Length inch	1.63 in

Force Related

Installation Torque Recommended in-lb	240 LBS/in
---------------------------------------	------------

General

Material Type - Screw Plated	DURIUM™ Silicon Bronze N
Sub Brand	MECHANICAL CONNECTOR
UPC	781810238967
Type	GD
U Bolt Type	261
Material	Copper Alloy, Cast
Plating Type	Unplated
UPC 12 Digit	781810238967
UPC 14 Digit GTIN	00781810238967

Logistics

Pallet Quantity	1
Carton Quantity	5

Product Assets

[Catalog \[English\]](#)