



FD67T12134NTN, Substation - Copper Stud Connector

By Burndy
Catalog # [FD67T12134NTN](#)

Copper Stud Connectors



Features

- High copper alloy stud connector allows bolting cable and tubing terminals to equipment studs
- Hex head captured bolts provide one-wrench installation
- One pad contact surface is on centerline of stud, pad is finished on both sides, all pads are 4-hole NEMA drilling

Application

Substation

Specifications

Standards - RoHS Compliance	UI
Status	
Certification - CSA Approved	No

Conductor

Conductor - Connection Combination	Stud to Bar
------------------------------------	-------------

Configuration

Physical Attribute - Pad Orientation	In-line
Physical Attribute - Pad Configuration	4 holes
Physical Attribute - Number of Holes	4

Connector Type	Stud Connector
----------------	----------------

Dimensions

Dimension - Pin Diameter inch	1.500 in
Dimension - Pin Diameter fraction	1-1/2
Dimension - Pad Width inch	3.00 in
Dimension - Height mm	0 mm
Dimension - F Width Center to Center inch	1.75 in
Dimension - Threads per inch	12

General

Plated	Y
Material - Hardware	DURIUM™ Silicon Bronze
UPC	621945126213
Type	Studs
Material	Copper Alloy
Plating Type	Tin - Electro Plated
UPC 12 Digit	621945126213
UPC 14 Digit GTIN	00621945126213

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)