




FD67T12144N, Substation - Copper Stud Connector

By Burndy

Catalog # [FD67T12144N](#)

Stud Connector, 1.50 IN Stud to 4 Holes Aluminum Bar, Material:
Cast Copper Alloy



Features

- High copper alloy stud connector allows bolting cable and tubing terminals to equipment studs
- Hex head captured bolts provide one-wrench installation
- One pad contact surface is on centerline of stud, pad is finished on both sides, all pads are 4-hole NEMA drilling

Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Connection Combination	Stud to Bar
------------------------------------	-------------

Configuration

Physical Attribute - Pad Orientation	In-line
Physical Attribute - Pad Configuration	4x3 - 4 holes
Physical Attribute - Number of Holes	4
Connector Type	Stud Connector

Dimensions

Dimension - Pin Diameter inch	1.50 in
Dimension - Pin Diameter fraction	1-1/2

Dimension - Pad Width inch	4.00 in
Package Height	0.000 in
Dimension - Height mm	0 mm
Dimension - Bolt Size fraction	1/2
Package Weight	0.000 lb.
Dimension - Width inch	4.00 in
Package Length	0.000 in
Dimension - F Width Center to Center inch	1.75 in
Package Width	0.000 in
Dimension - L Length Overall mm	165 mm
Dimension - B Length inch	2.69 in
Dimension - D inch	3.00 in
Dimension - N inch	0.62 in
Dimension - Threads per inch	12
Dimension - Length Overall inch	6.50 in

General

Plated	N
Material - Hardware	Durium
UPC	781810435021
Type	Studs
Material	Copper Alloy, Cast
Plating Type	Unplated
UPC 12 Digit	781810435021
UPC 14 Digit GTIN	00781810435021

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)