

GKA8C, Copper, Direct Burial Ground Terminal

By Burndy
Catalog # [GKA8C](#)



Cu Direct Burial Ground Terminal, #10 AWG Sol-#8 AWG Str, #10 Hole Size, Stainless Steel H/W

Features

- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - UL Listed Direct Burial	Yes
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	• 10 AWG • 9 AWG • 8 AWG
Conductor - Copper Solid Size	• 10 AWG • 9 AWG • 8 AWG • 7 AWG
Conductor - Copper Solid Size Range	10 AWG-7 AWG
Conductor Type	• CU C Str-Size • CU C Solid-Size
Conductor - Copper Str Size Range	10 AWG-8 AWG

Dimensions

Dimension - Pad Width inch	0.38 in
----------------------------	---------

Package Height	0.000 in
Dimension - Height mm	14.7 mm
Dimension - Height inch	0.58 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	21 mm
Dimension - Hole Size mm	5 mm
Dimension - Hole Size inch	0.21 in
Dimension - B Length inch	0.31 in
Dimension - N inch	0.19 in
Dimension - Length Overall inch	0.81 in

Force Related

Installation Torque	25 LBS/in
Recommended in-lb	

General

Material Type - Screw	Steel - Stainless
Physical Attribute - Screw Type	Slot
Plated	N
UPC	781810100981
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810100981
UPC 14 Digit GTIN	00781810100981

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)