



Gasoline Hydraulic Pump, 4 HP, 8 Quarts Reservoir Volume, 10000 psi

By Burndy
Catalog # [GP10](#)

Gasoline Hydraulic Pump, 4HP, 10000 psi



Features

- Heavy duty gasoline engine
- Sturdy steel roll cage design
- Manual control valve
- Quick disconnect hydraulic coupler
- 8 quart reservoir
- Oil level inspection window

Application

Pumping

Specifications

Buy American Compliant	Contact Manufacturer
EU RoHS Indicator	Yes
Standards - RoHS Compliance	EX
Status	
Buy America(n) Qualified	Contact Manufacturer

Dimensions

Length	21 in
Width	16 in
Weight	78 lb.

Height	22.25 in
Dimensions	21 in x 16 in x 22.25 in

General

Application - For Use On	Use with 10,000 psi Remote Hydraulic Crimpers and Cutters
Type	Pump
UPC 12 Digit	781810492758
UPC 14 Digit GTIN	00781810492758
Tool Type	Pump, Gas Hydraulic
UPC	781810492758

Logistics

Package Contents	Pump only
Minimum Pack Quantity	1

Operational

Power Source	• 4 HP • 4 Cycle Engine
--------------	---

Product Assets

[Catalog \[English\]](#)