



GQ291, Copper Ground Connector, 2/0 AWG Str-250 kcmil

By Burndy
Catalog # [GQ291](#)

Cast Cu Alloy Mechanical Grounding connectors, 2/0 AWG- 250 kcmil, 6" L, 2.75" W

Features

- Rated for Direct Burial in earth or concrete
- UL 467 Listed for the US and Canadian Markets
- One-wrench installation

Application

For Cross Connecting A Wide Range Of Copper Cable To Tube, Direct Burial In Earth Or Concrete

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance	CM
Status	
Certification - UL Listed Direct Burial	Yes
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor Size	2/0 AWG Str - 250 kcmil
Conductor Type	• CU Tube Std-Size • CU C Str-Size
Conductor - Copper Str Size Range	2/0 AWG - 250 kcmil

Dimensions

Package Height	0.000 in
Dimension - Height mm	173 mm
Dimension - Height inch	6.81 in



Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	152 mm
Dimension - Width fraction	2-3/4 in
Bolt Size	1/2 in
Dimension - Width mm	70 mm
Dimension - Width inch	2.75 in
Dimension - Length Overall inch	6.00 in

Force Related

Installation Torque Recommended	480 LBS/in in-lb
---------------------------------	------------------

General

Material Type - Screw	DURIUM™ Silicon Bronze
Plated	No
Sub Brand	MECHANICAL CONNECTOR
Product Type	Mechanical
UPC	781810233757
Type	GQ
U Bolt Type	• 392 • 291
Material	Copper Alloy, Cast
Plating Type	Unplated
UPC 12 Digit	781810233757
UPC 14 Digit GTIN	00781810233757

Logistics

Minimum Pack Quantity	2
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)