



FD68ACG3, Substation - Aluminum Stud Connector

By Burndy
Catalog # [FD68ACG3](#)

Substation Connectors

Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Connection Combination	Stud to Pad
------------------------------------	-------------

Configuration

Physical Attribute - Pad Orientation	In-line
Physical Attribute - Pad Configuration	4 holes
Physical Attribute - Number of Holes	4
Connector Type	Stud Connector

Dimensions

Dimension - Pin Diameter inch	2.000 in
Dimension - Pin Diameter fraction	2
Dimension - Pad Width inch	4.00 in
Package Height	0.000 in
Dimension - Height mm	73.9 mm

Dimension - Height inch	2.91 in
Package Weight	0.000 lb.
Dimension - Width mm	102 mm
Dimension - Width inch	4.00 in
Package Length	0.000 in
Dimension - F Width Center to Center inch	1.75 in
Package Width	0.000 in
Dimension - L Length Overall mm	192 mm
Dimension - B Length inch	2.50 in
Dimension - D inch	4.00 in
Dimension - N inch	0.88 in
Dimension - Threads per inch	12
Dimension - Length Overall inch	7.56 in

General

Plated	N
Material - Hardware	Aluminum
UPC	781810441169
Material	Aluminum Alloy
Plating Type	Unplated
UPC 12 Digit	781810441169
UPC 14 Digit GTIN	00781810441169

Logistics

Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)