



GSC632NH25B5H, Ground Stud, Tin Cast Cu, 90° offset NEMA

By Burndy
Catalog # [GSC632NH25B5H](#)

Ground Stud, Tin Plated Cast Copper, 90° offset NEMA Pad, 25 mm ball stud, Grade 5H

Features


- ASTM F855 Grade 5H Tested and Rated
- Third-party laboratory test results available
- 25mm Ball Stud
- 90° offset pad
- NEMA spacing for 1/2" Hardare
- Cast copper alloy
- Tin-plated for corrosion resistance
- Stud Cover Available - GSC632NH1BCOVER1

Specifications

Buy America(n) Qualified Contact Manufacturer

Dimensions

Height	1.38 in
Width	3.25 in



Length	5.69 in
Size	25mm Ball Stud
Dimensions	5.69 in x 3.25 in x 1.38 in

General

UPC	621945651098
Type	Safety Ground Stud
Material	Tin-Plated Copper

Logistics

Pallet Quantity	1332
Carton Quantity	6

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)