



GSTUD14HY Structural Steel Ground Stud, requires welding

By Burndy
Catalog # [GSTUD14HY](#)

Structural Steel Grounding Connector



Features

- May be welded to steel surfaces quickly and easily
- No disk grinding needed
- Knurled surface for better gripping
- Copper plated
- May be installed during adverse weather conditions

Application

For Compression Connectors And Mechanical Connectors

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - UL Listed Direct	No
Burial	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Rod Size Range	1/4 in
Conductor - Copper Str Size	6 AWG
Conductor - Rod Size	1/4 in
Conductor Type	• Rod-Size • CU C Str-Size
Conductor - Copper Str Size Range	6 AWG

Dimensions

Dimension - Ground Rod Size	1/4 in
Package Height	0.000 in

Dimension - Height mm	0 mm
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	122 mm
Physical Attribute - Tongue Angle	45 Degree
Dimension - B Length fraction	13/50 in
Dimension - B Length inch	0.26 in
Dimension - D inch	1.25 in
Dimension - Length Overall inch	4.81 in

General

Product Family	Grounding and Bonding Connectors>"Hyground" Compression Grounding Connectors>Cable to Steel/Bar VERSITAIL™
Trade Name	Yes
Plated	Yes
Sub Brand	HYGROUND, VERSITAIL
Product Type	Compression
UPC	781810220870
Type	GSTUD-HY
Material	Steel
Plating Type	Nickel
UPC 12 Digit	781810220870
UPC 14 Digit GTIN	00781810220870

Logistics

Minimum Pack Quantity	1
Pallet Quantity	9600
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)