



GZ4C38, Mechanical Grounding Connector, Copper Cable to Bar

By Burndy
Catalog # [GZ4C38](#)

Mechanical Grounding Connector, 8 AWG (Str) - 4 AWG (Str), 3/8" Stud

Features

- Rated for Direct Burial in earth or concrete
- UL 467 Listed for the US and Canadian Markets

Application

For Joining A Wide Range Of Copper Cable To Bar, Direct Burial In Concrete Or Ground

Specifications


Certification - UL Recognized	No
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - UL Listed Direct Burial	Yes
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	• 8 • 7 • 6 • 5 • 4
Conductor Range	#8 AWG (Str) to #4 AWG (Str)
Conductor - Copper Str Size Range	8 AWG - 4 AWG

Dimensions

Package Height	0.000 in
Dimension - Height mm	38.1 mm



Dimension - Height inch	1.50 in
Dimension - Height fraction	1-1/2
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	35 mm
Dimension - Width fraction	1-1/8 in
Bolt Size	3/8 in
Dimension - Bar Thickness mm	6 mm
Dimension - Bar Thickness inch	0.25 in
Dimension - Width mm	27 mm
Dimension - Width inch	1.06 in
Dimension - Length Overall inch	1.38 in

Force Related

Installation Torque	240 in-lb
Recommended in-lb	

General

Material Type - Screw Plated	DURIUM™ Silicon Bronze N
Sub Brand	MECHANICAL CONNECTOR
UPC	781810260753
Type	GZ
Material	Copper Alloy, Cast
Plating Type	Unplated
UPC 12 Digit	781810260753
UPC 14 Digit GTIN	00781810260753

Logistics

Pallet Quantity	9000
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)