

HFB444N, Substation - Copper Bar Clamp

By Burndy
Catalog # [HFB444N](#)

Substation Connectors



Features

- For use in bar clamp assembly
- Additional P1 assembly components needed to build your own high strength clamp assembly for multiple flat bar using the type HFB-P1 bar clamps and clamping hardware
- May be used in either indoor and outdoor applications

Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Configuration

Connector Type	Tap
----------------	-----

Dimensions

Dimension - Pin Diameter inch	4.00 in
Dimension - Pin Diameter fraction	4 in
Dimension - Pad Width inch	4.00 in
Package Height	0.000 in

Dimension - Height mm	0 mm
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	1.75 in
Package Width	0.000 in
Dimension - L Length Overall mm	232 mm
Dimension - B Length inch	4.00 in
Dimension - N inch	1.12 in
Dimension - Length Overall inch	9.12 in

General

Plated	N
UPC	781810005774
Material	Copper
Plating Type	Bright Dipped
UPC 12 Digit	781810005774
UPC 14 Digit GTIN	00781810005774

Logistics

Minimum Pack Quantity	1
Pallet Quantity	720
Carton Quantity	5

Product Assets

[Catalog \[English\]](#)