

HFB666N, Substation - Copper Bar Clamp

By Burndy
Catalog # [HFB666N](#)

Substation Connectors



Features

- For use in bar clamp assembly
- Additional P1 assembly components needed to build your own high strength clamp assembly for multiple flat bar using the type HFB-P1 bar clamps and clamping hardware
- May be used in either indoor and outdoor applications

Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Configuration

Connector Type	Tap
----------------	-----

Dimensions

Dimension - Pin Diameter inch	6.00 in
-------------------------------	---------

Dimension - Pin Diameter fraction	6 in
Dimension - Pad Width inch	6.00 in
Dimension - Height mm	0 mm
Dimension - L Length Overall mm	287 mm
Dimension - B Length inch	6.00 in
Dimension - N inch	1.12 in
Dimension - Length Overall inch	11.31 in

General

Plated	N
UPC	781810005750
Material	Copper
Plating Type	Bright Dipped
UPC 12 Digit	781810005750
UPC 14 Digit GTIN	00781810005750

Logistics

Minimum Pack Quantity	1
Pallet Quantity	336
Carton Quantity	4

Product Assets

[Catalog \[English\]](#)