



HSB34H48PF5, Heat Shrink Tubing, Heavy Wall, Black

By Burndy
Catalog # [HSB34H48PF5](#)

.75" ID Min (Expanded), .24" ID Max (Recovered), Black, Thick Wall, 4' Lengths, 5 Pieces per package

Features

- Heavy Wall Heat Shrink Tubing
- Shrink Ratio 3:1
- Inside diameter is coated with adhesive sealant to protect against moisture and corrosion
- 1500V
- UL486D Listed for Direct Burial

Application

For Direct Burial

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
EU RoHS Indicator	Yes
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Size	6AWG - 2AWG
Conductor Range	#6 AWG to #2 AWG

Configuration



Connector TypeHEAVY WALL TUBES

Current

Voltage Rating1500 V

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

General

Sub Brand	HEAT SHRINK
UPC	781810214893
Type	HS-H-PF, Heavy Wall, Flame Retardant
Material	Cross-linked Polyolefin

Logistics

Number of Pieces in Package	5
Pallet Quantity	36
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)