



HSB35H48PF5, Heat Shrink Tubing, Heavy Wall, Black

By Burndy
Catalog # [HSB35H48PF5](#)

.35" ID Min (Expanded), .15" ID Max (Recovered), Black, Thick Wall, Flame Retardant, 4' Length, 5 Pieces per package

Features

- Heavy Wall Heat Shrink Tubing
- Shrink Ratio 3:1
- Inside diameter is coated with adhesive sealant to protect against moisture and corrosion
- 1500V
- UL486D Listed for Direct Burial

Application

For Direct Burial

Specifications

Certification - ETL	No
Standards - RoHS Compliance Status	CM
Buy American Compliant	No
EU RoHS Indicator	Yes
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Size	14AWG - 10AWG
Conductor Range	#14 AWG to #10 AWG

Configuration



Connector TypeHEAVY WALL TUBES

Current

Voltage Rating1500 V

Dimensions

Package Height	4 in
Package Weight	6.75 lb.
Package Length	50 in
Package Width	4 in

General

Sub Brand	HEAT SHRINK
UPC	781810214886
Type	HS-H-PF, Heavy Wall, Flame Retardant
Material	Cross-linked Polyolefin

Logistics

Minimum Pack Quantity	5
Pallet Quantity	1080
Carton Quantity	5

Product Assets

[Catalog \[English\]](#)