



HSIC10500FR, Heat Shrink End Cap, Heavy Wall, FR, Black

By Burndy
Catalog # [HSIC10500FR](#)



2kV Rated, Fire Retardant, 1.10" ID Min (Expanded), .35" ID Max (Recovered), Thick Wall, 3" Long, Black

Features

- Heavy Wall Cross Linked Polyolefin
- UV94-V0
- Recognized Flame Retardant Material
- 3:1 Shrink Ratio
- Shrink Temperature of 150°C
- Blue Thermochromic lines disappear during correct installation
- Rated up to 2kV
- Sealing Adhesive
- Moisture and Water Resistant
- UL486D
- Insulates and Protects
- Direct Burial

Application

For Used To Insulating Exposed Conductors In Energized Applications

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Buy American Compliant	No
Certification - CSA Approved	No

Conductor

Conductor Size	1/0AWG - 500kcmil
Conductor Range	ConductorRange

Configuration

Connector Type	HEAVY WALL END CAP
----------------	--------------------

Current

Voltage Rating	2000 V
----------------	--------

Dimensions

Package Height	5.75 in
Length	3 in
Package Weight	2.4 lb.
Package Length	12.00 in
Package Width	9.00 in
Height	1.1 in
Width	1.1 in
Dimensions	3 in x 1.1 in x 1.1 in

General

Color	Black
Sub Brand	HEAT SHRINK
Product Type	Heavy Wall Black Polyolefin Heat Shrink End Cap
UPC	781810266557
Type	HSIC-FR, Heavy Wall, Fire Retardant
Material	Cross-linked Polyolefin

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1050
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)