



HSIC301000FR, Heat Shrink End Cap, Heavy Wall, FR, Black

By Burndy
Catalog # [HSIC301000FR](#)



2kV Rated, Fire Retardant, 1.5" ID Min (Expanded), .47" ID Max (Recovered), Thick Wall Heat Shrink End Cap, 3.5" Long, Black

Features

- Heavy Wall Cross Linked Polyolefin
- UV94-V0
- Recognized Flame Retardant Material
- 3:1 Shrink Ratio
- Shrink Temperature of 150°C
- Blue Thermochromic lines disappear during correct installation
- Rated up to 2kV
- Sealing Adhesive
- Moisture and Water Resistant
- UL486D
- Insulates and Protects
- Direct Burial

Application

For Used To Insulating Exposed Conductors In Energized Applications

Specifications

Standards - RoHS Compliance	CM
Status	
Buy American Compliant	No
Certification - CSA Approved	No

Conductor

Conductor Size	3/0AWG - 1000kcmil
Conductor Range	#2/0 AWG - 646 Kcmil

Configuration

Connector Type	HEAVY WALL END CAP
----------------	--------------------

Current

Voltage Rating	2000 V
----------------	--------

Dimensions

Package Height	16.00 in
Length	3.5 in
Package Weight	4.7 lb.
Package Length	10.25 in
Package Width	7.25 in
Height	1.5 in
Width	1.5 in
Dimensions	3.5 in x 1.5 in x 1.5 in

General

Color	Black
Sub Brand	HEAT SHRINK
Product Type	Heavy Wall Black Polyolefin Heat Shrink End Cap
UPC	781810266564
Type	HSIC-FR, Heavy Wall, Fire Retardant
Material	Cross-linked Polyolefin

Logistics

Minimum Pack Quantity	1
Pallet Quantity	630
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)