



FD80G11SV, Substation - Copper Stud Connector

By Burndy
Catalog # [FD80G11SV](#)

Copper Stud Connectors



Features

- For use on stud to pads
- Allows for bolting cable and tubing terminals to equipment studs
- Hex captured bolts provide one-wrench installation

Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Connection Combination	Stud to Pad
------------------------------------	-------------

Configuration

Physical Attribute - Pad Orientation	In-line
--------------------------------------	---------

Connector Type	Stud Connector
----------------	----------------

Dimensions

Dimension - Pin Diameter inch	6.000 in
Dimension - Pin Diameter fraction	6 in
Dimension - Height mm	0 mm
Dimension - Threads per inch	10

General

Plated	N
Material - Hardware	DURIUM™ Silicon Bronze
UPC	781810277966
Type	Studs
Material	Copper Alloy
Plating Type	Silver
UPC 12 Digit	781810277966
UPC 14 Digit GTIN	00781810277966

Logistics

Minimum Pack Quantity	30
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)