



FDA67D8, Substation - Copper Stud Connector

By Burndy
Catalog # [FDA67D8](#)

Copper Stud Connectors



Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Connection	Stud to Pad
Combination	

Configuration

Physical Attribute - Pad Orientation	90 Degree - horizontal
Physical Attribute - Pad Configuration	4x4 - 4 holes
Physical Attribute - Number of Holes	4
Connector Type	Stud Connector

Current

Amperage Rating	1450 A
-----------------	--------

Dimensions

Dimension - Pin Diameter inch	1.5 in
Dimension - Pin Diameter fraction	1-1/2 in

Dimension - Pad Width inch	4.00 in
Package Height	0.000 in
Dimension - Height mm	0 mm
Dimension - B Length fraction	2-9/50 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	179 mm
Dimension - B Length inch	2.18 in
Dimension - D inch	4.00 in
Dimension - N inch	1.12 in
Dimension - Threads per inch	12
Dimension - Length Overall inch	7.05 in

General

Plated	N
Material - Hardware	DURIUM™ Silicon Bronze
UPC	781810376386
Type	Studs
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810376386
UPC 14 Digit GTIN	00781810376386

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)