



K11A34U2, AL Universal Terminal, 2-Conductor, 2-Hole

By Burndy
Catalog # [K11A34U2](#)

2 Conductors: 4/0 AWG-500 kcmil, 2-Hole, 1/4" Stud, .69" Hole Spacing,
2 Screws, AL/CU, Tin Plated

Features

- Dual rated panelboard lugs
- Constructed from high strength, extruded aluminum alloy
- Electro tin-plated to provide low contact resistance

Application


For Aluminum and Copper Conductors

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
Buy America(n) Qualified	BABA Compliant (All status valid till December 2026)
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance	EX
Status	
Certification - UL Listed Direct Burial	No
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - AL Str Size	• 4/0 AWG • 250 kcmil • 266 kcmil • 300 kcmil • 336 kcmil • 350 kcmil • 397 kcmil • 400 kcmil • 450 kcmil • 477 kcmil • 500 kcmil
Conductor - AL Str Size Range	4/0 AWG-500 kcmil
Conductor - Copper Str Size	• 4/0 AWG • 250 kcmil • 300 kcmil • 350 kcmil • 400 kcmil • 450 kcmil • 500 kcmil
Conductor Size	4/0 AWG-500 KCMIL



Conductor - Copper Solid Size	4/0 AWG
Number Of Conductors	2
Conductor - Copper Solid Size Range	4/0 AWG
Conductor Type	• AL C Str-Size • CU C Str-Size • CU C Solid-Size
Conductor - Copper Str Size Range	4/0 AWG-500 kcmil

Configuration

Physical Attribute - Number of Holes	2
Connector Type	Stacked

Dimensions

Dimension - Pad Width inch	1.45 in
Package Height	3.250 in
Dimension - Height mm	61 mm
Dimension - Height inch	2.40 in
Dimension - Height fraction	2.4 in
Package Weight	2.980 lb.
Package Length	5.450 in
Package Width	4.750 in
Dimension - L Length Overall mm	74 mm
Dimension - Width fraction	1-11/25 in
Dimension - Hole Size mm	7 mm
Dimension - Hole Size inch	0.28 in
Dimension - Screw Size inch	15/16
Dimension - Stud Size inch	1/4 in
Dimension - Stud Size fraction	1/4
Dimension - Bolt Hole Size inch	0.25 in
Dimension - Bolt Size fraction	1/4
Dimension - Width mm	37 mm
Dimension - Width inch	1.44 in
Dimension - D inch	2.31 in
Dimension - N inch	0.25 in
Dimension - Length Overall inch	2.91 in

Force Related

Installation Torque Recommended	375 LBS/in in-lb
---------------------------------	------------------

General

Product Family	MECHANICAL
Material - Hardware	Aluminum

Physical Attribute - Screw Type	Allen
Plated	Yes
Sub Brand	UNIVERSAL TERM
Product Type	Terminal
UPC	781810370278
Type	Bolted Lugs & Terminals
Hex Key	3/8
Material	Aluminum
Plating Type	Tin
UPC 12 Digit	781810370278
UPC 14 Digit GTIN	00781810370278

Logistics

Minimum Pack Quantity	1
Pallet Quantity	90
Carton Quantity	90

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)



A Hubbell brand