



K21A36U2, AL Universal Terminal, 3-Conductor, 2-Hole

By Burndy
Catalog # [K21A36U2](#)

Aluminum Universal Terminal, 3 Conductor, 2 Holes, 2 AWG (Str)-600 kcmil, 3/8" Stud, 1.38" Spacing

Features

- Dual rated panelboard lugs
- Constructed from high strength, extruded aluminum alloy
- Electro tin-plated to provide low contact resistance

Application

For Aluminum and Copper Conductors

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	BABA Compliant (All status valid till December 2026)
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance	EX
Status	
Certification - UL Listed Direct Burial	No
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - AL Str Size	• 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 266 kcmil • 300 kcmil • 336 kcmil • 350 kcmil • 397 kcmil • 400 kcmil • 450 kcmil • 477 kcmil • 500 kcmil • 550 kcmil • 556 kcmil • 600 kcmil
Conductor - AL Str Size Range	2 Str. - 600 Kcmil



Conductor - Copper Str Size	• 2 AWG • 1 AWG • 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 300 kcmil • 350 kcmil • 400 kcmil • 450 kcmil • 500 kcmil • 550 kcmil • 600 kcmil
Number Of Conductors	3
Conductor Type	• AL C Str-Size • CU C Str-Size
Conductor - Copper Str Size Range	2 Str. - 600 Kcmil

Configuration

Physical Attribute - Number of Screws	3
Physical Attribute - Number of Holes	2
Connector Type	Stacked

Dimensions

Dimension - Pad Width inch	2.49 in
Package Height	0.000 in
Dimension - Height mm	77 mm
Dimension - Height inch	3.03 in
Dimension - Height fraction	3 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	125 mm
Dimension - Width fraction	2-1/2 in
Dimension - Hole Size mm	10 mm
Dimension - Hole Size inch	0.41 in
Dimension - Stud Size inch	3/8 in
Dimension - Bolt Hole Size inch	0.38 in
Dimension - Bolt Size fraction	3/8
Dimension - Width mm	64 mm
Dimension - Width inch	2.5 in
Dimension - D inch	2.31 in
Dimension - N inch	0.38 in

Dimension - Length Overall inch4.91 in

Force Related

Installation Torque Recommended375 LBS/in
in-lb

General

Product FamilyMECHANICAL
Material - HardwareAluminum
Physical Attribute - Screw TypeAllen
PlatedYes
Sub BrandUNIVERSAL TERM
Product TypeTerminal
UPC781810370322
TypeBolted Lugs & Terminals

MaterialAluminum
Plating TypeTin
UPC 12 Digit781810370322
UPC 14 Digit GTIN00781810370322

Logistics

Minimum Pack Quantity1
Pallet Quantity576
Carton Quantity18

Operational

Temperature Rating194

Product Assets

[Catalog \[English\]](#)



A Hubbell brand