



FDA67T1214, Substation - Copper Stud Connector

By Burndy
Catalog # [FDA67T1214](#)



Copper Stud Connectors

Application

Substation

Specifications

Standards - RoHS Compliance UI
Status
Certification - CSA Approved No

Conductor

Conductor - Connection Stud to Bar
Combination

Configuration

Physical Attribute - Pad 90 Degree - horizontal
Orientation
Connector Type Stud Connector

Dimensions

Dimension - Pin Diameter inch 1.5 in
Dimension - Pin Diameter 1-1/2 in
fraction
Dimension - Pad Width inch 4.00 in

Dimension - Height mm 0 mm
Dimension - L Length Overall 159 mm
mm
Dimension - D inch 3.00 in
Dimension - Threads per inch 12
Dimension - Length Overall 6.25 in
inch

General

Plated N
Material - Hardware DURIUM™ Silicon Bronze
UPC 621945251427
Type Studs
Material Copper Alloy
Plating Type Unplated
UPC 12 Digit 621945251427
UPC 14 Digit GTIN 00621945251427

Logistics

Minimum Pack Quantity 1

Product Assets

[Catalog \[English\]](#)