



K21A36U2N, AL Universal Terminal, 3-Conductor, 2-Hole

By Burndy
Catalog # [K21A36U2N](#)

3 Conductor #2 AWG-600 kmcil, 2 Hole, 1/2" holes, 1-3/4" spacing (NEMA-spacing), tin plated

Features

- AL9CU Dual Rated for both copper an aluminum conductor
- Listed to UL Wire Connector Standard UL486A-486B
- 1/2" diameter stud holes spaced 1-3/4" on center (NEMA-spacing)
- Range Taking conductor port

Application

Terminate multiple conductors onto equipment pads, panel boards, or switchgear

Specifications

Certification - ETL	No
Standards - RoHS Compliance	UI
Status	
Certification - CSA Approved	Yes

Configuration

Connector Type	Stacked
----------------	---------

Dimensions

Package Height	11.000 in
Dimension - Height mm	0 mm
Dimension - Bolt Size fraction	1/2
Length	5.34 in
Package Weight	25.800 lb.
Dimension - Width mm	0 mm
Package Length	16.800 in



Package Width	10.000 in
Dimension - L Length Overall mm	0 mm
Height	3 in
Width	2.47 in
Dimension - Thread Size	-
Dimension - Hole Size mm	0 mm
Dimensions	5.34 in x 2.47 in x 3 in

General

Plated	Y
UPC	781810538616
Type	Bolted Lugs & Terminals
Material	Aluminum
Plating Type	Tin - Electro Plated
UPC 12 Digit	781810538616
UPC 14 Digit GTIN	00781810538616

Logistics

Minimum Pack Quantity	65
Pallet Quantity	720
Carton Quantity	18

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)