



FDA67T1224TN, Substation - Copper Stud Connector

By Burndy
Catalog # [FDA67T1224TN](#)

Copper Stud Connectors



Application

Substation

Specifications

Standards - RoHS Compliance UI
Status
Certification - CSA Approved No

Conductor

Conductor - Connection Stud to Bar
Combination

Configuration

Physical Attribute - Pad Orientation 90 Degree - horizontal
Connector Type Stud Connector

Dimensions

Dimension - Pin Diameter inch 1.5 in
Dimension - Pin Diameter fraction 1-1/2 in
Dimension - Pad Width inch 4.00 in

Dimension - Height mm 0 mm
Dimension - L Length Overall mm 187 mm
Dimension - D inch 3.00 in
Dimension - Threads per inch 12
Dimension - Length Overall inch 7.38 in

General

Plated Y
Material - Hardware DURIUM™ Silicon Bronze
UPC 621945253490
Type Studs
Material Copper Alloy
Plating Type Tin - Electro Plated
UPC 12 Digit 621945253490
UPC 14 Digit GTIN 00621945253490

Logistics

Minimum Pack Quantity 1

Product Assets

[Catalog \[English\]](#)