



K22A39U2, AL Universal Terminal, 4-Conductor, 2-Hole

By Burndy
Catalog # [K22A39U2](#)

4 Conductor, kcmil, 3/8" Stud Class B&A, 1/0-750 kcmil Class B&C, 1/0-600 kcmil Class G,H,I,K, DLO, 2-Hole, 3/8" Stud, 1.38" Spacing, tin plated

Features

- Dual rated panelboard lugs
- Constructed from high strength, extruded aluminum alloy
- Electro tin-plated to provide low contact resistance

Application

For Aluminum and Copper Conductors

Specifications

EU RoHS Indicator	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	NC
Certification - UL Listed Direct Burial	No
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - AL Str Size	• 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 266 kcmil • 300 kcmil • 336 kcmil • 350 kcmil • 397 kcmil • 400 kcmil • 450 kcmil • 477 kcmil • 500 kcmil • 550 kcmil • 556 kcmil • 600 kcmil • 636 kcmil • 650 kcmil • 700 kcmil • 715 kcmil • 750 kcmil
Conductor - AL Str Size Range	1/0-750 Acmil



Conductor - Copper Str Size	• 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 300 kcmil • 350 kcmil • 400 kcmil • 450 kcmil • 500 kcmil • 550 kcmil • 600 kcmil • 700 kcmil • 750 kcmil
Number Of Conductors	4
Conductor Type	• AL C Str-Size • CU C Str-Size
Conductor - Copper Str Size Range	1/0-750 Acmil

Configuration

Physical Attribute - Number of Screws	4
Physical Attribute - Number of Holes	2
Connector Type	Stacked

Dimensions

Dimension - Pad Width inch	2.86 in
Package Height	0.000 in
Dimension - Height mm	76.7 mm
Dimension - Height inch	3.02 in
Dimension - Height fraction	3 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	125 mm
Dimension - Width fraction	3-3/50 in
Dimension - Hole Size mm	10 mm
Dimension - Hole Size inch	0.41 in
Dimension - Stud Size inch	3/8 in
Dimension - Bolt Hole Size inch	0.38 in
Dimension - Bolt Size fraction	3/8
Dimension - Width mm	78 mm

Dimension - Width inch	2.86 in	Type	Bolted Lugs & Terminals
Dimension - D inch	2.31 in	Material	Aluminum
Dimension - N inch	0.38 in	Plating Type	Tin plated
Dimension - Length Overall	4.91 in	UPC 12 Digit	781810370339
inch		UPC 14 Digit GTIN	00781810370339
Force Related		Logistics	
Installation Torque	375 LBS/in	Pallet Quantity	576
Recommended in-lb		Carton Quantity	18
General		Operational	
Material - Hardware	Aluminum	Temperature Rating	194
Physical Attribute - Screw Type	Allen		
Plated	Y		
Sub Brand	UNIVERSAL TERM	Product Assets	
UPC	781810370339	Catalog [English]	



A Hubbell brand