



K22A39U2N, AL Universal Terminal, 4-Conductor, 2-Hole

By Burndy
Catalog # [K22A39U2N](#)

Aluminum Universal Terminal, 2 Hole, 1/2" diameter stud holes spaced 1-3/4" on center (NEMA-spacing), tin plated

Features

- AL9CU Dual Rated for both copper an aluminum conductor
- Listed to UL Wire Connector Standard UL486A-486B
- 1/2" diameter stud holes spaced 1-3/4" on center (NEMA-spacing)
- Range Taking conductor port

Application

Terminate multiple conductors onto equipment pads, panel boards, or switchgear

Specifications

Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	UI
Industry Standard(s)	UL 486A-486B
Certification - CSA Approved	Yes

Conductor

Conductor Type	• AL C Str-Size • CU C Str-Size
----------------	---

Configuration

Connector Type	Stacked
----------------	---------

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Dimension - Bolt Size fraction	1/2



Length	5.34 in
Package Weight	0.000 lb.
Dimension - Width mm	0 mm
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	0 mm
Height	3 in
Width	2.75 in
Dimension - Thread Size	-
Dimension - Hole Size mm	0 mm
Dimensions	5.34 in x 2.75 in x 3 in

General

Plated	Y
UPC	781810670163
Type	Bolted Lugs & Terminals
Material	Aluminum
Plating Type	Tin - Electro Plated
UPC 12 Digit	781810670163
UPC 14 Digit GTIN	00781810670163

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	18

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)