



K33B344N, Copper, Multiple Outlet Transformer Terminal, 4-Holes, 1/2" Holes, NEMA Spacing, 4/0 Str-500 kcmil Copper

By Burndy
Catalog # [K33B344N](#)

Cast Cu Alloy URD Multiple Transformer Terminal, 4 NEMA Holes, 4/0 Str - 500 kcmil Cu Cable, 9/16" Hole Dia.

Features

- 4 NEMA Drilled Holes
- TIn Plated

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	EX
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size Range	4/0 AWG-500 kcmil
Conductor - Copper Str Size	• 4/0 AWG • 250 kcmil • 300 kcmil • 350 kcmil • 400 kcmil • 450 kcmil • 500 kcmil

Configuration

Physical Attribute - Number of Holes	4
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	3 in
Package Height	0.000 in
Dimension - Hole Size fraction	14/25
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	1.75 in
Package Width	0.000 in
Dimension - D inch	3 in
Dimension - N inch	0.62 in
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	7.09 in

General

Plated	Y
Trade Name	KA-LUG™
UPC	781810189207
Material	Copper Alloy
Plating Type	Tin
UPC 12 Digit	781810189207
UPC 14 Digit GTIN	00781810189207

Logistics

Minimum Pack Quantity	3
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)