



K3A36U2N, AL Universal Terminal, 3-Conductor, 2-Hole

By Burndy
Catalog # [K3A36U2N](#)

3-Conductor, 2-Hole, 1/2" Stud, 1.75" Spacing, #2 AWG-600 kcmil, Tin Plated

Features

- Dual rated lugs
- Constructed from high strength aluminum alloy
- Electro tin plating proving low contact resistance

Application

For Aluminum and Copper Conductors

Specifications

Buy American Compliant	Yes
Buy America(n) Qualified	• Buy America Compliant (All status valid till December 2026) • Buy American Act Compliant (All status valid till December 2026) • BABA Compliant (All status valid till December 2026)
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance	EX
Status	
Certification - UL Listed Direct Burial	No
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - AL Str Size	• 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 266 kcmil • 300 kcmil • 336 kcmil • 350 kcmil • 397 kcmil • 400 kcmil • 450 kcmil • 477 kcmil • 500 kcmil • 550 kcmil • 556 kcmil • 600 kcmil
-------------------------	---



Conductor - AL Str Size Range	2 Str. - 600 Kcmil
Conductor - Copper Str Size	• 2 AWG • 1 AWG • 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 300 kcmil • 350 kcmil • 400 kcmil • 450 kcmil • 500 kcmil • 550 kcmil • 600 kcmil
Conductor Size	2 AWG-600 KCMIL
Number Of Conductors	3
Conductor Type	• AL C Str-Size • CU C Str-Size
Conductor - Copper Str Size Range	2 Str. - 600 Kcmil

Configuration

Physical Attribute - Number of Screws	3
Physical Attribute - Number of Holes	2
Connector Type	Parallel Set-Screw

Dimensions

Dimension - Pad Width inch	3.64 in
Package Height	3.450 in
Dimension - Height mm	39.6 mm
Dimension - Hole Size fraction	9/16
Dimension - Height inch	1.56 in
Dimension - Height fraction	1.5555555555555556 in
Package Weight	2.220 lb.
Package Length	5.450 in
Package Width	4.750 in
Dimension - L Length Overall mm	119.12 mm
Dimension - Width fraction	3-63/100 in
Dimension - Hole Size mm	14 mm
Dimension - Hole Size inch	0.56 in
Dimension - Stud Size inch	1/2 in
Dimension - Bolt Hole Size inch	0.57 in
Dimension - Bolt Size fraction	1/2
Dimension - Width mm	92 mm

Dimension - Width inch	3.64 in
Dimension - D inch	3.22 in
Dimension - N inch	0.63 in
Dimension - Length Overall inch	4.69 in

Force Related

Installation Torque Recommended in-lb	375 LBS/in
---------------------------------------	------------

General

Product Family	MECHANICAL
Material - Hardware	Aluminum
Physical Attribute - Screw Type	Slot
Plated	Yes
Sub Brand	UNIVERSAL TERM
Product Type	Terminal
UPC	781810601204

Type	Bolted Lugs & Terminals
Material	Aluminum
Plating Type	Tin
UPC 12 Digit	781810601204
UPC 14 Digit GTIN	00781810601204

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1152
Carton Quantity	36

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)



A Hubbell brand