



GA25H26, Mech Ground Conn for Copper Cable to H-Beam

By Burndy
Catalog # [GA25H26](#)

Mechanical Ground Connector for Copper Cable to "H" Beam

Features

- High copper alloy ground connector
- Joins wide range of cable parallel to "H" beams or square tube
- Silicon bronze for superior corrosion protection

Application

For Joining A Wide Range Of Copper Cable Parallel To H Beams Or Square Tube

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size	4 AWG
Conductor - Copper Solid Size	4 AWG
Range	
Conductor Type	• CU C Solid-Size • CU C Str-Size
Conductor - Copper Str Size Range	2/0 AWG
Conductor - Copper Str Size	2/0 AWG

Dimensions

Package Height	0.000 in
----------------	----------

Dimension - Height mm	120.7 mm
Dimension - Height inch	4.75 in
Dimension - Height fraction	4-3/4 in
Package Weight	0.000 lb.
Dimension - Width mm	102 mm
Dimension - Width inch	4.00 in
Package Length	0.000 in
Package Width	0.000 in

Force Related

Installation Torque Recommended	240 Lb in
Run in-lb	

General

Plated	No
Sub Brand	MECHANICAL CONNECTOR
Product Type	Mechanical
UPC	781810001677
Type	GA-H
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810001677
UPC 14 Digit GTIN	00781810001677

Logistics

Minimum Pack Quantity	6
Pallet Quantity	1080
Carton Quantity	6

Product Assets

[Catalog \[English\]](#)