



KA26U2G1, AL Set Screw Terminal, #14-2/O Str, Dual Rated

By Burndy
Catalog # [KA26U2G1](#)

Mechanical Connector



Features

- Dual rated panelboard lugs constructed from high strength extruded aluminum alloy , electro tin-plated to provide low contact resistance

Specifications

Standards - Industry Standards	UL 486A-486B
Met	
Standards - RoHS Compliance	UI
Status	
Industry Standard(s)	UL 486A-486B
Certification - CSA Approved	Yes

Conductor

Conductor - AL Str Size Range	#14 AWG to 2/O kcmil
Conductor Type	- AL C Str-Size - CU C Str-Size
Conductor - Copper Str Size Range	#14 AWG to 2/O kcmil

Configuration

Physical Attribute - Number of Screws	1
Physical Attribute - Number of Holes	2
Number Of Ports	1
Connector Type	Terminal

Current

Rating - Minimum Voltage	600
--------------------------	-----

Dimensions

Dimension - Height mm	0 mm
Dimension - Height inch	0.88
Dimension - Width inch	0.63
Dimension - N inch	0.31
Dimension - Hole Size inch	0.27
Dimension - Length Overall inch	2.06

General

Physical Attribute - Screw Type	Slot
Plated	Y
UPC	781810653968
Type	Bolted Lugs & Terminals
Material	Aluminum
Plating Type	Tin - Electro Plated
UPC 12 Digit	781810653968
UPC 14 Digit GTIN	00781810653968

Logistics

Minimum Pack Quantity	1
-----------------------	---

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)