

KA34TN, Copper Terminal, 1-Hole, 1/2" Stud, Tin Plated

By Burndy
Catalog # [KA34TN](#)

Accommodates: #4 - 500 kcmil; 1-Hole, 1/2" Stud; 375 in-lb recommended torque



Features

- Compact
- Economical
- Tin-plated

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor Type	CU C Str-Size
Conductor - Copper Str Size Range	4/0 AWG-500 kcmil
Conductor - Copper Str Size	• 4/0 AWG • 250 kcmil • 300 kcmil • 350 kcmil • 400 kcmil • 450 kcmil • 500 kcmil

Configuration

Physical Attribute - Number of Screws	1
Physical Attribute - Number of Holes	1
Connector Type	Terminal

Current

Rating - Minimum Voltage	600
--------------------------	-----

Dimensions

Dimension - Pad Width inch	1.38 in
Package Height	0.000 in
Dimension - Height mm	53.1 mm
Dimension - Height inch	2.09 in
Dimension - Height fraction	2-8/89 in
Dimension - B Length fraction	1-3/25 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	65 mm
Dimension - B Length inch	1.12 in
Dimension - N inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	2.55 in
Dimension - Stud Size inch	1/2

Force Related

Installation Torque	375 LBS/in
Recommended in-lb	

General

Physical Attribute - Screw Type	Allen
Plated	Y
UPC	781810095195
Type	Bolted Lugs & Terminals
Material	Copper
Plating Type	Tin - Electro Plated
Hardware Type	13/16 UNF Socket/HexScrew
UPC 14 Digit GTIN	00781810095195

Logistics

Minimum Pack Quantity	1
Pallet Quantity	288
Carton Quantity	18

Product Assets

[Catalog \[English\]](#)