



KA4CTN, Copper Mechanical Terminal, 1-Hole, Tin Plated

By Burndy
Catalog # [KA4CTN](#)



#14 Solid - #4 Stranded Copper; 1/4" Stud; 45 in-lb recommended torque; Tin plated

Features

- Compact, high copper alloy terminal for joining cable to equipment pads or terminal blocks
- Tin plated

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper Solid Size	• 14 AWG • 13 AWG • 12 AWG • 11 AWG • 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG
Conductor - Copper Solid Size Range	14 AWG-4 AWG
Conductor Type	• CU C Str-Size • CU C Solid-Size
Conductor - Copper Str Size	• 14 AWG • 12 AWG • 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG

Configuration

Physical Attribute - Number of Screws	1
Physical Attribute - Number of Holes	1
Connector Type	Terminal

Current

Rating - Minimum Voltage	600
--------------------------	-----

Dimensions

Dimension - Pad Width inch	0.54 in
Package Height	0.000 in
Dimension - Height mm	19.6 mm
Dimension - Height inch	0.77 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	28 mm
Dimension - B Length inch	0.47 in
Dimension - N inch	0.25 in
Dimension - Hole Size mm	7 mm
Dimension - Hole Size inch	0.28 in
Dimension - Length Overall inch	1.11 in
Dimension - Stud Size inch	1/4

Force Related

Installation Torque Recommended in-lb	45
---------------------------------------	----

General

Physical Attribute - Screw Type	Slot
Plated	Y
Material - Hardware	Steel
UPC	781810244463
Type	Bolted Lugs & Terminals
Material	Copper
Plating Type	Tin - Electro Plated
Hardware Type	5/16 UNF Slotted SetScrew
UPC 14 Digit GTIN	00781810244463

Logistics

Minimum Pack Quantity	1
-----------------------	---



A Hubbell brand