



KC22TN, SERVIT POST Mech Conn, Cable to Flat, Tin Plated

By Burndy
Catalog # [KC22TN](#)



Mechanical SERVIT POST™ Connector; Cable to Flat

Features

- SERVIT POST tin-plated mechanical connector used to ground 1 or 2 cables to steel structures, fence posts, and transformers
- Also used to tap 1 or 2 cables from bus bar
- 1-Wrench installation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size	• 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG
Conductor - Copper Solid Size Range	2 AWG-10 AWG
Physical Attribute - Number of Conductors Accommodated Total	1
Conductor - Copper Str Size Range	3 AWG-10 AWG
Conductor - Copper Str Size	• 10 AWG • 9 AWG • 8 AWG

- 7 AWG
- 6 AWG
- 5 AWG
- 4 AWG
- 3 AWG

Dimensions

Dimension - Height mm	25.4 mm
Dimension - Height inch	1.00 in
Dimension - Body Width inch	0.62 in
Dimension - Width inch	25 mm
Dimension - P inch	0.26 in
Dimension - L Length Overall mm	41 mm
Dimension - B Length inch	0.46 in
Dimension - Nut Width inch	0.75 in
Dimension - D inch	0.63 in
Dimension - Length Overall inch	1.62 in

Force Related

Stud Installation Torque inch pounds	280 LBS/in
--------------------------------------	------------

General

Plated	N
Trade Name	SERVIT POST™
UPC	781810210161
Type	KC and K2C Series
Material	Bronze, Leaded, Commercial
Plating Type	Leaded Bronze Alloy
UPC 12 Digit	781810210161
UPC 14 Digit GTIN	00781810210161

Logistics

Minimum Pack Quantity	1
Pallet Quantity	14850
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)