



GAR8626W, Mech Ground Conn, Cable to Rod or Pipe, Tin Plated

By Burndy

Catalog # [GAR8626W](#)

Mechanical Grounding Connector, Cable to Rod or Pipe, 4 AWG (Sol)- 2/0 AWG (Str), 6" Pipe, Tin Hot Dipped



Features

- Wire to Rebar
- Fence Post Grounding Connector
- Wire to Pipe
- One-wrench installation
- Rated for Direct Burial in earth or concrete
- UL467 Listed for US and Canadian Markets
- Select connectors qualified to IEEE-837-2014

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Pipe or Round Tube Size	6 in
Conductor - Copper Solid Size	• 4 • 3 • 2 • 1 • 1/0 • 2/0 • 3/0
Conductor - Copper Solid Size Range	4 AWG - 2/0 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size • CU Tube Std-Size • Rod-Size
Conductor - Copper Str Size Range	5 AWG - 2/0 AWG
Conductor - Copper Str Size	• 5 • 4 • 3

- 2
- 1
- 1/0
- 2/0

Conductor - Copper Tube Std Size Range

Conductor - Copper Tube Std Size

Dimensions

Package Height	0.000 in
Dimension - Height mm	63.5 mm
Dimension - Height inch	2.50 in
Package Weight	0.000 lb.
Dimension - Width mm	213 mm
Dimension - Width inch	8.38 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	43 mm
Dimension - B Length inch	1.25 in
Dimension - Outside Diameter inch	6.63 in
Dimension - Length BB inch	1.69 in
Dimension - Length Overall inch	1.69 in

Force Related

Installation Torque Recommended in-lb	480 lb-in
---------------------------------------	-----------

General

Plated	Y
Material - Hardware UPC	DURIUM™ Silicon Bronze 781810117071
Material Plating Type	Copper Alloy Tin - Hot Dipped
UPC 12 Digit	781810117071
UPC 14 Digit GTIN	00781810117071

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	1



A Hubbell brand