



KC26B1TN, SERVIT POST Mech Conn, Cable to Flat, Tin Plated

By Burndy
Catalog # [KC26B1TN](#)



SERVIT POST™ Connector; Copper Cable to Flat, #2-2/0 AWG Str or #2-3/0 AWG Solid, 1/2" Stud, Tin Plated

Features

- SERVIT POST tin-plated mechanical connector used to ground 1 or 2 cables to steel structures, fence posts, and transformers
- Also used to tap 1 or 2 cables from bus bar
- 1-Wrench installation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size	• 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG • 3/0 AWG
Conductor - Copper Solid Size Range	2 AWG-3/0 AWG
Physical Attribute - Number of Conductors Accommodated Total	1
Conductor - Copper Str Size Range	2 AWG-2/0 AWG
Conductor - Copper Str Size	• 2 AWG • 1 AWG

- 1/0
- 2/0 AWG

Dimensions

Dimension - Height mm	35.1 mm
Dimension - Height inch	1.38 in
Dimension - Body Width inch	0.88 in
Dimension - P inch	0.44 in
Dimension - L Length Overall mm	67 mm
Dimension - B Length inch	1.04 in
Dimension - Nut Width inch	1.04 in
Dimension - D inch	1.25 in
Dimension - Length Overall inch	2.62 in

Force Related

Stud Installation Torque inch pounds	480 LBS/in
--------------------------------------	------------

General

Plated	Y
Trade Name	SERVIT POST™
UPC	781810002117
Type	KC and K2C Series
Material	Bronze, Leaded, Commercial
Plating Type	Tin Plated
UPC 12 Digit	781810002117
UPC 14 Digit GTIN	00781810002117

Logistics

Pallet Quantity	5800
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)