



GB34T3TN, Mech Ground Conn, Cable to Bar, Tin Plated

By Burndy
Catalog # [GB34T3TN](#)

Mechanical Grounding Connector, Cable to 0.63" - 0.814" Thick Bar, 300 kcmil - 500 kcmil, 1/2" Stud, Tin - Plated



Features

- Mechanical Grounding Connector
- Cable to 0.63"-0.814" Thick Bar
- 300-500 kcmil
- 1/2" Stud
- Tin Plated

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	UL467
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size Range	300 KCMIL - 500 KCMIL
Conductor - Copper Str Size Range	300 kcmil - 500 kcmil
Conductor - Copper Str Size	• 300 kcmil • 350 kcmil • 400 kcmil • 450 kcmil • 500 kcmil

Dimensions

Package Height	0.000 in
Dimension - Height mm	63.5 mm
Dimension - Height inch	2.50 in
Package Weight	0.000 lb.
Dimension - Width inch	2.34 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	38 mm
Dimension - Width fraction	2-1/3 in
Dimension - Length Overall inch	1.50 in

Force Related

Installation Torque	360 lb-in
Recommended in-lb	

General

Physical Attribute - Screw Type	Oval Shank Bolt
Plated	Y
UPC	781810424063
Material Type - Screw Material	DURIUM™ Silicon Bronze Copper Alloy
Plating Type	Tin - Electro Plated
UPC 12 Digit	781810424063
UPC 14 Digit GTIN	00781810424063

Product Assets

[Catalog \[English\]](#)