



GB34T8TN, Mech Ground Conn, Cable to Bar, Tin Plated

By Burndy
Catalog # [GB34T8TN](#)

Mechanical Grounding Connector, Cable to 1/4" - 1" Thick Bar, 300 kcmil - 500 kcmil, 1/2" Stud, 2-1/3" Width, Tin Plated



Features

- High copper alloy ground connector for joining a range of cable to 1/4" thick bar
- Type GB separates cable from bar
- One-wrench installation
- UL467 Listed, Suitable for Direct Burial in earth or concrete

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size Range	300 KCMIL - 500 KCMIL
Conductor - Copper Str Size Range	300 kcmil - 500 kcmil
Conductor - Copper Str Size	• 300 kcmil • 350 kcmil • 400 kcmil • 450 kcmil • 500 kcmil

Dimensions

Package Height	0.000 in
Dimension - Height mm	84.3 mm
Dimension - Height inch	3.32 in
Package Weight	0.000 lb.
Dimension - Width inch	2.31 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	35 mm
Dimension - Width fraction	2-1/3 in
Dimension - Length Overall inch	1.38 in

Force Related

Installation Torque	480 lb-in
Recommended in-lb	

General

Physical Attribute - Screw Type	Hexagonal Bolt
Plated	Y
UPC	781810117590
Material Type - Screw	DURIUM™ Silicon Bronze
Material	Copper Alloy
Plating Type	Tin - Electro Plated
UPC 12 Digit	781810117590
UPC 14 Digit GTIN	00781810117590

Logistics

Minimum Pack Quantity	1
Pallet Quantity	432
Carton Quantity	12

Product Assets

[Catalog \[English\]](#)