




KK3A44U2N, AL Universal Terminal, 3-Conductor, 2-Hole

By Burndy
Catalog # [KK3A44U2N](#)

Aluminum Universal Terminal, 3 Conductor, 2 Hole, 500-1000 kcmil, 1/2" Stud, 1.75" Stud Hole Spacing, 6 Screws, Al/Cu Rated, Tin Plated

Features

- Dual rated panelboard lugs constructed from high strength extruded aluminum alloy , electro tin-plated to provide low contact resistance

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	NC
Certification - UL Listed Direct Burial	No
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Number Of Wires	3
Conductor - AL Str Size	500 kcmil 550 kcmil 556 kcmil 600 kcmil 636 kcmil 650 kcmil 700 kcmil 715 kcmil 750 kcmil 795 kcmil 800 kcmil 874 kcmil 900 kcmil 954 kcmil 1000 kcmil
Conductor - AL Str Size Range	500 - 1000 Kcmil
Conductor Size	500-1000 KCMIL
Conductor Type	- CU C Str-Size - AL C Str-Size
Conductor - Copper Str Size Range	500 - 1000 Kcmil

Configuration

Physical Attribute - Number of Holes	2
Connector Type	Parallel Set-Screw

Dimensions

Dimension - Pad Width inch	4.79 in
Dimension - Height mm	48.3 mm
Dimension - Hole Size fraction	9/16
Dimension - Height inch	1.90 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	157 mm
Dimension - Hole Size mm	14 mm
Dimension - Hole Size inch	0.56 in
Dimension - Stud Size inch	0.56 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - Bolt Size fraction	1/2
Dimension - N inch	0.63 in
Dimension - Length Overall inch	6.19 in

General

Material - Hardware Plated	Aluminum Y
UPC	781810601488
Type	Bolted Lugs & Terminals
Material	Aluminum
Plating Type	Tin Plated
UPC 14 Digit GTIN	00781810601488

Logistics

Minimum Pack Quantity	1
Pallet Quantity	12
Carton Quantity	12

Product Assets

[Catalog \[English\]](#)