



GBL30GS, Mech Ground Conn, Cable to Bar, Galvanized Steel

By Burndy
Catalog # [GBL30GS](#)

Cast Copper Alloy Ground Connector, 4 AWG Sol - 300 kcmil, 1/2" Stud, 1-1/2" Width, Galvanized Steel Hardware

Features

- Cast Copper Alloy Ground Connector
- 4 AWG (Sol)-300 kcmil
- 1/2" Stud
- Galvanized Steel Hardware

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size	• 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG
Conductor - Copper Solid Size Range	4 AWG - 300 KCMIL
Conductor - Copper Str Size Range	4 AWG - 300 kcmil
Conductor - Copper Str Size	• 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 300 kcmil

Dimensions

Package Height	0.000 in
Dimension - Height mm	58.9 mm
Dimension - Height inch	2.32 in
Package Weight	0.000 lb.
Dimension - Width mm	38 mm
Dimension - Width inch	1.50 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	48 mm
Dimension - Hole Size inch	0.56 in
Dimension - Bus Thickness inch	0.32 in
Dimension - Length Overall inch	1.88 in
Dimension - Stud Size inch	33/64

Force Related

Installation Torque	480 lb-in
Recommended in-lb	

General

Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Material - Hardware	Galvanized Steel
UPC	781810100912
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810100912
UPC 14 Digit GTIN	00781810100912

Logistics

Minimum Pack Quantity	24
Pallet Quantity	4536
Carton Quantity	12

Product Assets

[Catalog \[English\]](#)