



KPA25G8, Pressure Bar Cu Lug, 1-Hole, Tin Plated

By Burndy

Catalog # [KPA25G8](#)

Cu Terminal with Pressure Bar, 1-Hole, 5/16" Stud, #4-1/0 Str, 1-Hole, Tin Plated



Features

- High copper alloy terminal (tin-plated) for joining a wide range of cable to equipment pads or terminal blocks
- Tongue and body are 1-piece design, pressure bar equalizes pressure over the conductor and prevents the screw from cutting into the cable

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper Solid Size	• 14 AWG • 13 AWG • 12 AWG • 11 AWG • 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG
Conductor Type	• CU C Str-Size • CU C Navy-Size
Conductor - Copper Str Size Range	14 AWG-4 AWG
Conductor - Copper Str Size	• 14 AWG • 12 AWG • 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG

Configuration

Physical Attribute - Number of Screws	1
Physical Attribute - Number of Holes	1
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	0.75 in
Package Height	0.000 in
Dimension - Height mm	31.8 mm
Dimension - Height inch	1.25 in
Dimension - Height fraction	1-1/4 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	43 mm
Dimension - D inch	0.81 in
Dimension - N inch	0.41 in
Dimension - Hole Size mm	10 mm
Dimension - Hole Size inch	0.41 in
Dimension - Length Overall inch	1.70 in

Force Related

Installation Torque Recommended in-lb	180
---------------------------------------	-----

General

Plated	Y
Trade Name	SCRULUG™
UPC	781810035542
Type	Bolted Lugs & Terminals
Material	Copper
Plating Type	Tin
UPC 14 Digit GTIN	00781810035542

Logistics

Minimum Pack Quantity	1
Pallet Quantity	17400
Carton Quantity	100



A Hubbell brand