



KPA4CTPG2, Mechanical Pressure Bar Style Copper Lug, 1-Hole

By Burndy
Catalog # [KPA4CTPG2](#)



Copper Alloy SCRULUG with Pressure Bar, 1-Hole, 1/4" Hole, #14 - #6 AWG, Tin Plated

Features

- High copper alloy terminal (tin-plated) for joining a wide range of cable to equipment pads or terminal blocks
- Tongue and body are 1-piece design, pressure bar equalizes pressure over the conductor and prevents the screw from cutting into the cable

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size	• 14 AWG • 13 AWG • 12 AWG • 11 AWG • 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG
Conductor - Copper Solid Size Range	14 AWG-6 AWG
Conductor - Copper Str Size Range	14 AWG-6 AWG
Conductor - Copper Str Size	• 14 AWG • 12 AWG • 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG

Configuration

Physical Attribute - Number of Screws	1
Physical Attribute - Number of Holes	1
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	0.50 in
Package Height	0.000 in
Dimension - Height mm	25.4 mm
Length	1.28 in
Dimension - Height inch	1.00 in
Dimension - Height fraction	1 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	33 mm
Height	1 in
Width	0.5 in
Dimension - D inch	0.71 in
Dimension - N inch	0.33 in
Dimension - Hole Size mm	7 mm
Dimension - Hole Size inch	0.28 in
Dimension - Length Overall inch	1.28 in
Dimension - Strip Length inch	9/16
Dimension - Stud Size inch	1/4
Dimensions	1.28 in x 0.5 in x 1 in

Force Related

Installation Torque	45 LBS/in
Recommended in-lb	

General

Physical Attribute - Screw Type	Slot
Plated	N
Trade Name	SCRULUG™
UPC	781810076972
Type	Bolted Lugs & Terminals
Material	Copper
Plating Type	Tin
Hardware Type	5/16 Dia.Slot Robertson
UPC 14 Digit GTIN	00781810076972

Logistics

Minimum Pack Quantity	100
Pallet Quantity	1
Carton Quantity	1



A Hubbell brand