



KPA8C, Pressure Bar Style Copper Lug, 1-Hole

By Burndy
Catalog # [KPA8C](#)

Cu Mechanical Terminal, 1-Hole, #10 Stud, #14 Sol-8 AWG Str, Tin Plated



Features

- High copper alloy terminal (tin-plated) for joining a wide range of cable to equipment pads or terminal blocks
- Tongue and body are 1-piece design, pressure bar equalizes pressure over the conductor and prevents the screw from cutting into the cable

Application

For Joining A Wide Range Of Copper Cable To Equipment Pads Or Terminal Blocks

Specifications

Certification - UL Recognized	No
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
Certification - UL Listed Direct Burial	No
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper Str Size	• 14 AWG • 12 AWG • 10 AWG • 9 AWG • 8 AWG
Conductor Size	14-8 AWG
Conductor - Copper Str Navy Size Range	4 (1) Navy-14 (140) Navy
Conductor - Copper Str Navy Size	• 4 (1) Navy • 4 (7) Navy • 4 (19) Navy • 4 (41) Navy • 6 (7) Navy • 6 (19) Navy • 9 (7) Navy • 9 (37) Navy • 14 (7) Navy • 14 (140) Navy

Conductor - Copper Solid Size	• 14 AWG • 13 AWG • 12 AWG • 11 AWG • 10 AWG • 9 AWG • 8 AWG
Conductor - Copper Solid Size Range	14 AWG-8 AWG
Conductor Type	• CU C Str-Size • CU C Solid-Size
Conductor - Copper Str Size Range	14 AWG-8 AWG

Configuration

Physical Attribute - Number of Screws	1
Physical Attribute - Number of Holes	1
Connector Type	Pressure Bar

Dimensions

Dimension - Pad Width inch	0.38 in
Package Height	0.000 in
Dimension - Height mm	18.3 mm
Dimension - Height inch	0.72 in
Dimension - Height fraction	18/25 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	25 mm
Dimension - Hole Size mm	5 mm
Dimension - Hole Size inch	0.21 in
Dimension - Stud Size inch	#10
Dimension - Bolt Size fraction	#10
Dimension - Width mm	10 mm
Dimension - Width inch	0.38 in
Dimension - D inch	0.47 in
Dimension - N inch	0.22 in
Dimension - Length Overall inch	0.97 in

Force Related

Installation Torque Recommended in-lb	25 LBS/in
---------------------------------------	-----------

General

Trade Name	SCRULUG™
Physical Attribute - Screw Type	Slot
Plated	Y
Sub Brand	SCRULUG
UPC	781810353455
Type	Bolted Lugs & Terminals
Material	Copper

Plating Type	Tin
UPC 14 Digit GTIN	00781810353455

Logistics

Carton Quantity	100
-----------------	-----

Product Assets

[Catalog \[English\]](#)



A Hubbell brand