



GC2626CT, Mech Ground Connector, One to Two Cables to Bar

By Burndy
Catalog # [GC2626CT](#)

Cable Tray Ground Clamp, Cast Cu Alloy, #2 Sol-2/0 Str Al/Cu, with 3/8" Stud, Galvanized Steel Hardware, Tin Plated

Features

- Cable Tray Ground Clamp of tin-plated cast copper
- Accommodates either one or two conductors, copper or aluminum cable
- Low profile head with deep Phillips recess
- Galvanized steel bolt has ribbed neck preventing rotation during installation when installed in a 0.44 diameter hole
- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets with copper conductor only

Application


For Direct Burial Applications In Concrete Or Earth And For Used With Aluminum Or Galvanized Steel Cable Tray

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards	UL467
Met	
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size	• 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG
Conductor - Copper Solid Size Range	2 AWG-2/0 AWG
Conductor - AL Str Size	• 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG



Conductor - AL Str Size Range	2 AWG-2/0 AWG
Conductor - Copper Str Size Range	2 AWG-2/0 AWG
Conductor - Copper Str Size	• 2 AWG • 1 AWG • 1/0 • 2/0 AWG

Dimensions

Package Height	0.000 in
Dimension - Height mm	49.5 mm
Dimension - Height inch	1.95 in
Package Weight	0.000 lb.
Dimension - Width mm	43 mm
Dimension - Width inch	1.70 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	1.12 in
Dimension - Cross Flats inch	0.56 in

Force Related

Installation Torque	240 LBS/in
Recommended in-lb	

General

Plated	Y
Sub Brand	MECHANICAL CONNECTOR
UPC	781810220573
Type	GC-CT
Material	Copper Alloy
Plating Type	Tin Plated
UPC 12 Digit	781810220573
UPC 14 Digit GTIN	00781810220573

Logistics

Pallet Quantity	5400
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)