



KS23TN, Split Bolt Connector, Run: #6-#1 AWG, Tap: #14-1 AWG, Tin Plated

By Burndy
Catalog # [KS23TN](#)

Cu Alloy SERVIT Split Bolt, #6 - #1 AWG(Run), #14 - #1
AWG(Tap), Tin Plated

Features


- UL467 Listed for Direct Burial applications in earth or concrete
- Compact, high-strength, copper alloy with free-running threads and easy to grip wrench flats
- Highly resistant to cracking and corrosion

Specifications

Standards - Industry Standards Met	UL486D
Standards - RoHS Compliance Status	CM
Industry Standard(s)	UL486D
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Run Range	6 STR - 2 STR
Conductor - Copper Solid Run	1 AWG
Conductor - Copper Solid Tap	1 AWG
Conductor Type	• CU C Solid-Run • CU C Str-Run • CU Weld C Str-Run • CU C Solid-Tap • CU C Str-Tap • CU Weld C Str-Tap



Conductor - Copper Str Tap Range	6 STR - 2 STR
----------------------------------	---------------

Configuration

Connector Type	Split Bolt
----------------	------------

Dimensions

Width	0.62 in
Dimension - Length Overall inch	1.54

General

Plated	Y
Trade Name	SERVIT®
UPC	781810054253
Material	Copper
Plating Type	Tin Plated
UPC 12 Digit	781810054253
UPC 14 Digit GTIN	00781810054253

Logistics

Minimum Pack Quantity	1
Pallet Quantity	17400
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)