



GC2929TN, Mech Ground, Two Cables to Bar, Tin Plated

By Burndy
Catalog # [GC2929TN](#)



Mechanical Grounding Connector, 2 Cables to 1/4" Thick Bar, 2/0 AWG (Sol) -250 kcmil, 1/2" Stud, Torque: 480 lb in, Tin Plated

Features

- Mechanical Grounding Connector
- 2 Cables to 1/4" Thick Bar
- 2/0 AWG Sol-250 kcmil
- 1/2" Stud

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size	• 2/0 AWG • 3/0 AWG • 4/0 AWG
Conductor - Copper Solid Size Range	2/0 AWG - 250 KCMIL
Conductor - Copper Str Size Range	2/0 AWG - 250 kcmil
Conductor - Copper Str Size	• 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil

Dimensions

Package Height	0.000 in
Dimension - Height mm	58.9 mm
Dimension - Height inch	2.32 in
Package Weight	0.000 lb.
Dimension - Width mm	52 mm
Dimension - Width inch	2.04 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	32 mm
Dimension - Width fraction	2 in
Dimension - Length Overall inch	1.25 in

Force Related

Installation Torque	480 lb-in
Recommended in-lb	

General

Physical Attribute - Screw Type	Hexagonal Bolt
Plated	Y
UPC	781810079409
Material Type - Screw	DURIUM™ Silicon Bronze
Material	Copper
Plating Type	Tin - Electro Plated
UPC 12 Digit	781810079409
UPC 14 Digit GTIN	00781810079409

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	12

Product Assets

[Catalog \[English\]](#)