



KS26NK, Split Bolt Connector, Run/Tap: #2 AWG-2/0 AWG Str, Nickel Plated

By Burndy
Catalog # [KS26NK](#)

Copper Split Bolt, Cu: 2 AWG-2/0 AWG (Str) (Run & Tap); Nickel Plated

Features

- UL467 Listed for Direct Burial applications in earth or concrete
- Compact, high-strength, copper alloy with free-running threads and easy to grip wrench flats
- Highly resistant to cracking and corrosion


Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	• UL 486A • UL486B
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	• UL 486A • UL486B
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor Type	• CU C Solid-Run • CU C Str-Run • CU Weld C Solid-Run • CU Weld C Str-Run • CU C Str-Tap • CU Weld C Solid-Tap • CU Weld C Str-Tap • CU C Solid-Tap
----------------	---

Configuration



Connector Type	Split Bolt
----------------	------------

Dimensions

Dimension - Width mm	21 mm
Dimension - Width inch	0.82 in
Dimension - L Length Overall mm	49 mm
Dimension - B Length inch	.90 in
Dimension - Cross Flats inch	1.05 in
Dimension - Width fraction	41/50 in
Dimension - Length Overall inch	1.94 in

Force Related

Installation Torque Recommended in-lb	385 in
---------------------------------------	--------

General

Plated	Y
Trade Name	SERVIT®
UPC	781810354797
Material	Copper
Plating Type	Nickel
UPC 12 Digit	781810354797
UPC 14 Digit GTIN	00781810354797

Logistics

Minimum Pack Quantity	1
Pallet Quantity	11600
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)