




KS29G4, Split Bolt Connector, Run: #1 AWG
Str-250 kcmil, Tap: #8 AWG-250 kcmil

By Burndy
Catalog # [KS29G4](#)

Cu Alloy SERVIT Split Bolt, #1 AWG - 250 kcmil(Run), #8 AWG - 250 kcmil(Tap)



Features

- UL467 Listed for Direct Burial applications in earth or concrete
- Compact, high-strength, copper alloy with free-running threads and easy to grip wrench flats
- Highly resistant to cracking and corrosion

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL486D
Standards - RoHS Compliance Status	EX
Certification - cULus	No
Industry Standard(s)	UL486D
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor Type	• CU C Solid-Run • CU C Str-Run • CU Weld C Str-Run • CU C Solid-Tap • CU C Str-Tap • CU Weld C Str-Tap
----------------	---

Configuration

Connector Type	Split Bolt
----------------	------------

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

General

Plated	Y
Trade Name	SERVIT®
UPC	781810054314
Material	Copper
Plating Type	Tin
UPC 12 Digit	781810054314
UPC 14 Digit GTIN	00781810054314

Logistics

Minimum Pack Quantity	34
Pallet Quantity	3200
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)