



KVSU26, Mechanical Connector with Spacer Bar

By Burndy
Catalog # [KVSU26](#)

Tin plated copper alloy with tin plated hardware; spacer bar to separate dissimilar conductors

Features

- Compact, tin-plated high strength copper alloy connector with spacer and tin-plated silicon bronze hardware
- Recommended for heavy duty connections
- Spacer separates dissimilar conductors and provides long contact length
- Neoprene ring prevents loss of shorter bolt during installation
- Longer peened bolt permits swivel action for easier installation
- CSA Listed for Copper

Application

For All Combinations of Copper, Aluminum, ACSR, AAAC And 5005, Heavy Duty Connections

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	EX
Status	
UL Listed	No
Certification - CSA Approved	Yes

Conductor

Conductor - Galvanized Steel Str Tap Range	3/16 in-7/16 in
Conductor - Galvanized Steel Str Run Range	5/16 in-7/16 in
Conductor - AL Str Run Range	2 str. - 2/0 str.
Conductor - AL Str Tap Range	6 str.- 2/0 str.
Conductor - ACSR Str Run Range	3 ACSR - 2/0 ACSR
Conductor - ACSR Str Tap Range	6 ACSR - 2/0 ACSR
Conductor - Copper Str Run Range	2 str. - 2/0 str.
Conductor - Copper Solid Run Range	1 AWG-3/0 AWG
Conductor - Copper Solid Run	• 1 AWG • 1/0 AWG • 2/0 AWG • 3/0 AWG
Conductor - Copper Solid Tap Range	6 AWG-3/0 AWG
Conductor - Copper Solid Tap	• 6 AWG • 5 AWG



	• 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG • 3/0 AWG
Conductor - CopperWeld Solid Tap Range	6 sol.- 3/0 sol.
Conductor - CopperWeld Solid Run Range	1 sol.- 3/0 sol.
Conductor Type	• AL C Str-Run • AL C Str-Tap • CU C Str-Run • CU C Str-Tap • AAAC C 5005-Run • AAAC C 5005-Tap • AAAC C 6201-Run • AAAC C 6201-Tap • ACSR C Str-Run • ACSR C Str-Tap • CU C Solid-Run • CU C Solid-Tap • GAL Steel C Str-Run • GAL Steel C Str-Tap • Cu Weld Sol.- Run • Cu Weld Sol.- Tap
Conductor - Copper Str Tap Range	6 str.- 2/0 str.

Dimensions

Package Height	0.000 in
Dimension - Height mm	50.80 mm
Dimension - Height inch	2.00 in
Dimension - Height fraction	2 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	25 mm
Dimension - Width fraction	1-1/2 in
Dimension - Stud Size inch	5/16 in
Dimension - Width mm	38 mm
Dimension - Width inch	1.56 in
Dimension - Length Overall inch	1.06 in

Force Related

Installation Torque Recommended 180 LBS/in
in-lb

General

Product Family Power Connectors>Split
Bolts>KVSU

Trade Name OKLIP™

Plated Yes

Sub Brand OKLIP

Product Type Mechanical

UPC 781810081105

Type KVSU, Universal

Construction Material - Main High Copper Alloy

Material Copper

Plating Type Tin

UPC 12 Digit 781810081105

UPC 14 Digit GTIN 00781810081105

Logistics

Minimum Pack Quantity 1

Pallet Quantity 4500

Carton Quantity 25

Product Assets

[Catalog \[English\]](#)

